








PCB LAYOUT
RECOMMENDED



General Specification
Current Rating: 1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment
Standard Temperature: -20°C~+70°C
Industrial Temperature: -40°C~+85°C
Humidity: 20~70%
Contact Resistance: $\leq 30m\Omega$
Insulation Resistance: $\geq 500M\Omega$
Dielectric Strength: 500V AC / (50Hz) /Min
Mating And Unmating Force: 3~20N
Durability: 750 Cycles Min

Material Specification
Housing : Thermo-plastic, UL94V-0.
Contact : Alloy Copper
Shield : Alloy Copper
Please refer to the customer drawing when customer has specified

网络插座外形图



温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

序号	名称	材料	数量	镀层/颜色	备注
3	插针	PHOSPHOR BRONZE	8	1U"	
2	外壳	304	1	NI	
1	塑座	LCP	1	BLACK	

绘图: 吴鹏飞 日期: 2022.6.30

审核: 陈伟强 日期:

核准: 陈伟强 日期:

一般公差
30~ ±0.25
10~30 ±0.20
~10 ±0.15
角度: ±2°

品名: RCH-SF39 (无灯无弹)
料号: SP39-80002021LB16 (RC02437)
型号: RJ45
图号:

版本: 1 of 1
单位: mm
比例: 1:1
纸张: A4

版本: A/0

变更履历

变更单号

绘制

日期

核准

日期

版本

单位

比例

纸张

图号

