







Electrical
Contact Resistance: <5mΩ
Insulation strength: 1 kVdc
Frequency range: 1-100 MHz
Insulation resistance: >0.5 GΩ
Single contact rated current: 1.5A
rated voltage: <30 V
Transmission performance: Class D
Meet the criteria: TIA/EIA 568B, IEC11801

Mechanical
Insertion force: ≤ 30 N
Pull out the force: ≤ 30 N
Service life: > 1000 plugging
Panel thickness: Max. 3mm 0.12
Wiring: vertical PCB installation
Locking device: Latch Lock
Installation direction: rear installation
Base Shape: A
Mounting: A-Screw

Material
Plating of outerwire: 0.2 um Au over Ni plating
Contact: bronze (Gum)
Inner core: LCP 125 GR
The shell: PA66 125 GR

Environmental
Flammability: UL 94 V-0
Solderability: comply with IEC 608-20
Operating temperature: -30°C to 80°C

PCB LAYOUT
RECOMMENDED

网络插座外形图

温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

序号	名称	材料	数量	镀层/颜色	备注
7	接插	不锈钢	1	NI	
6	弹片	铜	1	NI	
5	内弹片	H62	1	NI	
4	排针	PHOSPHOR BRONZE	8	1U"	
3	后盖	LCP	1	BLACK	
2	面板	PA66	1	BLACK	董(白)色
1	塑座	PA66	1	BLACK	

绘图: 吴家飞 日期: 2022.6.6

品名: RCH-INZ 圆形带锁 90°

审核: 陈伟 日期:

料号: KNZ-80000051AB35 (WR44183)

核准: 陈伟 日期:

型号: RJ45 图号:

该图面供温州瑞川电子有限公司内部使用,不得私自复印

版本: 1 of 1 单位:mm 比例: 1:1 纸张: A4