








A-A

PCB LAYOUT

**General Specification**  
Current Rating: 1.5A DC /Contact, 20mA DC for LED signals  
Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals  
Operating Environment:  
Standard Temperature: -20℃~+70℃  
Industrial Temperature: -40℃~+85℃  
Humidity: 20~70%  
Contact Resistance: ≤30mΩ  
Insulation Resistance: ≥500MΩ  
Dielectric Strength: 500V AC/(50HZ)/Min  
Mating And Unmating Force: 3~20N  
Durability: 750 Cycles Min

**Material Specification**  
Housing :Thermo-plastic, UL94V-0.  
Contact :Alloy Copper  
Shield :Alloy Copper  
Please refer to the customer drawing when customer has specified

|    |    |                 |    |       |    |
|----|----|-----------------|----|-------|----|
| 3  | 后盖 | PBT             | 1  | WHITE |    |
| 2  | 插针 | PHOSPHOR BRONZE | 8  | "3U"  |    |
| 1  | 塑座 | PBT             | 1  | WHITE |    |
| 序号 | 名称 | 材料              | 数量 | 镀层/颜色 | 备注 |



温州瑞川电子有限公司  
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

|       |        |         |                               |         |        |
|-------|--------|---------|-------------------------------|---------|--------|
| 一般公差  | 品名:    | RJ45 白色 |                               |         |        |
| 90~   | ±0.25  | 料号:     | SP18KW-80000003PW30 (RC02416) |         |        |
| 10~30 | ±0.20  | 型号:     | RJ45                          | 图号:     |        |
| ~10   | ±0.15  | 版本:     | 单位:mm                         | 比例: 1:1 | 纸张: A4 |
| 角度:   | ±2°    | 版本:     | 单位:mm                         | 比例: 1:1 | 纸张: A4 |
| 页面:   | 1 of 1 | 版本:     | 单位:mm                         | 比例: 1:1 | 纸张: A4 |

网络插座外形图

|     |     |
|-----|-----|
| 绘图: | 日期: |
| 审核: | 日期: |
| 核准: | 日期: |

A/0 新出版发行

变更履历

变更单号

绘制 日期

核准: 日期:

该图面供温州瑞川电子有限公司内部使用, 不得私自复印