



Connectors > Connector Accessories > Connector Seals & Cavity Plugs > DEUTSCH Sealing Plugs



Connector Seal & Plug Type: **Keying Plug**
Primary Product Material: **PBT**
Primary Product Color: **White**
Resistance to Hydrocarbons: **Good**
Operating Temperature (Max): **125 °C [257 °F]**

[All DEUTSCH Sealing Plugs \(10\)](#)

Features

Product Type Features

Connector Seal & Plug Type	Keying Plug
----------------------------	-------------

Body Features

Primary Product Material	PBT
Primary Product Color	White

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	20000
Packaging Method	Box

Other

Resistance to Hydrocarbons	Good
Contains Lubricant	No



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-J41-DDRC
DEUTSCH DT Receptacle Connectors



TE Part # CAT-H3930-CH8172
DEUTSCH HD30 Housings



TE Part # CAT-H396-CH8172
DEUTSCH HDP20 Housings



TE Part # CAT-D799-CH8172
DEUTSCH DRC Housings



TE Part # CAT-H3910-CH8172
DEUTSCH HD10 Housings



TE Part # CAT-J41-DDPC
DEUTSCH DT Plug Connectors



TE Part # CAT-D781-CH8172
DEUTSCH DRB Housings



TE Part # CAT-ST858-CH8172
DEUTSCH Strike Housings



 TE Part # HDP24-24-21PE-L015 REC, 21P, BLK, E, THD, 12/16, P	 TE Part # HDP24-24-19PE-L015 REC, 19P, BLK, E, THD, 12/16, P	 TE Part # HDP24-24-19SE-L017 REC, 19P, BLK, E, RNG, 12/16, S	 TE Part # HDP24-24-14PE-L017 REC, 14P, BLK, E, RNG, 4/12/16, P
 TE Part # HDP24-24-14PN-L017 REC, 14P, BLK, N, RNG, 4/12/16, P	 TE Part # HDP24-24-14SN-L017 REC, 14P, BLK, N, RNG, 4/12/16, S	 TE Part # HDP24-24-18PN-L015 REC, 18P, BLK, N, THD, 8/12/16, P	 TE Part # HDP24-24-18PN-L017 REC, 18P, BLK, N, RNG, 8/12/16, P
 TE Part # HDP24-24-18SN-L015 REC, 18P, BLK, N, THD, 8/12/16, S	 TE Part # HDP24-24-18SN-L017 REC, 18P, BLK, N, RNG, 8/12/16, S	 TE Part # HDP24-24-19SN-L015 REC, 19P, BLK, N, THD, 12/16, S	 TE Part # HDP24-24-19SN-L017 REC, 19P, BLK, N, RNG, 12/16, S

Also in the Series

DEUTSCH HD

 Automotive Connector Caps & Covers (32)	 Automotive Housings(742)	 Connector Backshells(29)	 Connector Seals & Cavity Plugs(10)
 Connector Strain Relief(5)	 Insertion & Extraction Tools(11)	 Other Automotive Connector Accessories(11)	 PCB Headers & Receptacles(1)

Also in the Series

DEUTSCH HD30



Automotive Connector Caps & Covers (14)

Automotive Housings(359)

Connector Backshells(2)

Connector Seals & Cavity Plugs(11)

Connector Strain Relief(5)

Insertion & Extraction Tools(10)

Other Automotive Connector Accessories(6)

Customers Also Bought

TE Part #HD36-24-9PN-059
PLG,9P,AL,N, CBLCLMPBT,DRAIN,4/8 /12,P,MC

TE Part #HDP24-24-21PN
DEUTSCH HDP20 Housings

TE Part #35152
TERMINAL,PIDG SPD 12-10 8

TE Part #962371-1
ABDECKKAPPE F42/29P

TE Part #282189-5
SPLASH PROOF CONN. W.S.L.

TE Part #3-2293551-1
62POS,MIXED,REC HSG,ASSY,SLD

TE Part #8-1419167-0
1X4 SEALD HARN ASSY W/O CPA

TE Part #2600025-1
DEUTSCH DT-XT Wedge Locks

Documents

Product Drawings
SEALING PLUG, SIZE 16, KEYING, WHT
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_0413-215-1605_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_0413-215-1605_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_0413-215-1605_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

CONNECTOR SELECTOR

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English