






PC Board Layout
Top View

General Specification
Current Rating:1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating:125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment
Standard Temperature: -20℃~+70℃
Industrial Temperature: -40℃~+85℃
Humidity: 20~70%
Contact Resistance:≤30mΩ
Insulation Resistance:≥500MΩ
Dielectric Strength:500V AC/(50HZ)/Min
Mating And Unmating Force:3~20N
Durability:750 Cycles Min

Material Specification
Housing :Thermo-plastic, UL94V-0.
Contact :Alloy Copper
Shield :Alloy Copper
Please refer to the customer drawing when customer has specified

网络插座外形图

绘图: 吴鹏飞 日期: 2022.4.7
审核: 陈德 日期:
核准: 陈德 日期:
该图面供温州瑞川电子有限公司内部使用,不得私自复印



温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

序号	名称	材料	数量	镀层/颜色	备注
1	插座	PBT	1	BLACK	
2	插针	PHOSPHOR BRONZE	8	"FU"	

一般公差	品名	料号	型号	图号
>80~				
±0.45				
>10~30				
±0.35				
~10				
±0.25				
角度: ±5°				
版本: 1 of 1				
单位:mm				
比例: 1:1				
纸张: A4				

版本: A/0
变更履历: 新出版发行