






PRODUCT NO: DS810MCS0020

REV	DESCRIPTION	DWN	DATE	APPROVEN
A	FIRST ISSUE	chen	2021/6/18	John kine
B	更改产品本体压花位置	chen	2021/10/9	John kine



CRIMP TUBE

SPECIFICATIONS:

IMPEDANCE: 50 ohms
 FREQUENCY RANGE: 0~3GHZ
 WORKING VOLTAGE: 500V RMS@SEA LEVEL
 INSULATION RESISTANCE: 1000 ohms min
 TEMPERATURE RANGE: -55°C TO +165°C
 CONTACT RESISTANCE: INNER CONDUCTOR 5 mΩ
 EXTERNAG CONDUCTOR 2.5 mΩ
 VOLTAGE STANDING WAVE RATIO: ≤ 1.2(0~3GHZ)
 INSERT LOSS: ≤ 0.15dB

1	BODY	BRASS	GOLD	1
2	INSULATOR	TEFION	---	1
3	CONTACT PIN	BRASS	GOLD	1
4	CRIMP TUBE	BRASS	NICKEL	1
5				
6				
7				
8				
9				
10				
NO	COMPONENT NUMBER	MATERIAL	FINISH	QTY

NOTE:		TOIERANCE	UNLESS OTHER WISPECIFIED TOLERANCES FDR INCHES ARE 0.5-8MM±0.010MM 8-30MM±0.15MM 30-120MM±0.3MM
DRAWN	2021/10/9	VIEW	
CHECKED		UNIT	MM
APPROVALS		SCALE	1 : 1

DOSIN DOSIN INDUSTRIAL(HK)CO.,LTD 东莞市德索五金电子有限公司 Dongguan Dosin Hardware Electronics Co.,Ltd.		Web: http://www.dosinconn.com dosin2005@dosin-china.com E-mail: dosin2005@163.com Tel: (0086)769-81153906 Fax: (0086)769-81875836	
NAME: MMCX PLUG FOR RG316 RG174 CABLE		SIZE A PRODUCT NO: DS810MCS0020 SIZE B	
DATE TIME 2021/10/9		CAD FILE H/companydrawings/BD SHEET: 1 OF 1	