










RECOMMENDED PCB PATTERN DIM.
TOLERANCE : ± 0.05



COVER OPEN STATE




APPLICABLE F.F.C DIMENSION (REF.)
THICKNESS 0.3±0.03



NOTES:

- 1.HUOSINGT:LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BEIGE
- 2.ACTUATOR:LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
- 3.TERMINAL: PHOSPHOR BRONZE
PLATING:GOLD FLASH OR MATTE-TIN OR TIN (LEAD FREE)
- 4.FITTING NAIL: BRASS
PLATING:MATTE-TIN OR TIN (LEAD FREE)
- 5.CODING INFORMATION: XDFC-0520B-***P



CABLE INSERT DIM.
SECTION: A-A

PIN	Dimensions			
	A	B	C	D
10	9.81	4.50	5.57	8.43
11	10.31	5.00	6.07	8.93
12	10.81	5.50	6.57	9.43
13	11.31	6.00	7.07	9.93
14	11.81	6.50	7.57	10.43
15	12.31	7.00	8.07	10.93
16	12.81	7.50	8.57	11.43
17	13.31	8.00	9.07	11.93
18	13.81	8.50	9.57	12.43
19	14.31	9.00	10.07	12.93
20	14.81	9.50	10.57	13.43
21	15.31	10.00	11.07	13.93
22	15.81	10.50	11.57	14.43
23	16.31	11.00	12.07	14.93
24	16.81	11.50	12.57	15.43
25	17.31	12.00	13.07	15.93
26	17.81	12.50	13.57	16.43
27	18.31	13.00	14.07	16.93
28	18.81	13.50	14.57	17.43
29	19.31	14.00	15.07	17.93
30	19.81	14.50	15.57	18.43
31	20.31	15.00	16.07	18.93
32	20.81	15.50	16.57	19.43
33	21.31	16.00	17.07	19.93
34	21.81	16.50	17.57	20.43
35	22.31	17.00	18.07	20.93
36	22.81	17.50	18.57	21.43
37	23.31	18.00	19.07	21.93
38	23.81	18.50	19.57	22.43
39	24.31	19.00	20.07	22.93
40	24.81	19.50	20.57	23.43

深圳市连欣科技有限公司

版本: B	图幅: A4	未标注公差:	产品料号:
单位: mm	比例: 5:1	X.X ±0.10	XDFC-0520B-***P
张数: 1 OF 1		X.XX ±0.05	产品品名:
定位片改为共用款	Kavin 09.25.14'	X.XXX ANG. 0°30'	0.5mm掀盖式FPC-带扣
修订	修改摘要	绘图:	审核:
签名	日期		核准: