




Product NO.		DOSIN-809-0017		
REV	DESCRIPTION	DWN	DATE	APPROVEN
A	First issue	Mr. CHEN	2021/12/20	John kine
B				



Specifications

Impedance: 50 Ohms

Frequency Range: 0~6Ghz


VSWR: 1.5max

Working Voltage: <170 V rms @ sea level

Insulation Resistance: 5000 Ohms min

Temperature Range: -65°C TO +165°C

Drawings products are in line with ROHS standards



1	Body	Brass	GOLD	1	NOTE:	Tolerance	X. ±0.10	Dosin Industrial(H.K)Co.Ltd E-mail: dosin2005@163.com dosin2005@dosin-china.com 东莞市德索五金电子制品有限公司 Web: http://www.china-guan.com Dosin Hardware Electronics Co.,Ltd TEL: (0086)769-81153906 FAX: (0086)769-81875836
2	Insulation	PTFE	White	1			X. X ±0.08	
3	Pin	Brass	GOLD	1			X. XX ±0.05	
4					DRAWN	2021/12/20	Angular ±5°	Name: MMCX JACK PCB SIZE A Product NO. DOSIN-809-0017 REV A DateTime 2021/12/20 CAD FILE D/company drawings/BD SHEET: 1 OF 1
5								
6					chen		View	
7					CHECKED		UNIT	
8					APPROVALS	28/07.2016	SCALE	1:1
9								
10					John			
NO	Component Number	Material	Finish	QTY				