

Specification Sheet

Part Number: 251-30409



Can be cut to length with scissors, eliminating waste and keeping stock to a minimum.
Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.

Grommet, Panel Thickness 0.130"-0.189", PTFE, Natural, 9.7ft/pkg

Article Number	251-30409
Type	G51TD
Color	Natural (NA)
Quantity Per	reel
Product Description	HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.
Short Description	Grommet, Panel Thickness 0.130"-0.189", PTFE, Natural, 9.7ft/pkg
Global Part Name	G51TD-PTFE-NA

Length L (Imperial) 9.7

Variant Open

Width W (Imperial) 0.331

Width W (Metric) 8.4

Height H (Imperial) 0.244

Height H (Metric) 6.2

Panel Thickness Min (Imperial) 0.13

Panel Thickness Max (Imperial) 0.19

Panel Thickness Min (Metric) 3.3

Panel Thickness Max (Metric) 4.8

Material Polytetrafluoroethylene (PTFE)

Material Shortcut PTFE

US MIL SPEC MS21266-4T

Flammability UL 94 V-0

Halogen Free No

UV Resistant (Yes/No)	No
Operating Temperature	-76°F to +500°F (-60°C to +260°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	9.7
Package Quantity (Metric)	3
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).