




NOTE:

1.ELECTRICAL:

1.1.Rated Voltage:250V

1.2.Rated Current:4A

1.3.Contact Resistance:≤15mΩ

1.4.Insulation Resistance:≥100MΩ

1.5.Rated impulse voltage:2500V

2.ENVIRONMENTAL:

2.1.Operating Temperature: -25°C TO +85°C

2.2.Protection Grade:IP67,When Tight Locked

2.3.Pollution Degree:3

3.Contact Material: Brass NI Plated Under Gold Flash Plated

4.Cable Range:22-20AWG

5.Conform to IEC 61076-2-101

* UNLESS OTHERWISE SPECIFIED
TOLERANCES ON DECIMAL IS:

X. ± 0.50 X° ± 2°

X.X ± 0.30

X.XX ± 0.20

All dimensions are in mm			Material:															
			Finishing:															
<table border="1"> <tr> <td>Signature</td> <td>Date</td> </tr> <tr> <td>Created by</td> <td></td> </tr> <tr> <td>Checked by</td> <td></td> </tr> <tr> <td>Approved by</td> <td></td> </tr> <tr> <td>State</td> <td>First Release</td> </tr> </table>			Signature	Date	Created by		Checked by		Approved by		State	First Release	Phase Marking		Weight	Scale	拓宜(上海)工控电器设备有限公司 Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.	
			Signature	Date														
Created by																		
Checked by																		
Approved by																		
State	First Release																	
			1:1															
			P/N		61054007		Part Name:											
			MD/CD				C12B-FSD-RM1-4SCUP											
							Rev.	Page:										
							01	1 OF 1										