


Specification Sheet

Part Number: 3N9C



Sheathing allows flexible routing and lead-out of cables
The inner edges are beveled preventing damage to cables
Sheathing is reusable and resistant to most chemicals
Spiralwrap is U.L. Recognized

Spiralwrap Protective Sheathing, 0.5" Diameter, PA6, Natural, 100 ft/roll

Article Number	161-05051
Type	3N
Color	Natural (NA)
Quantity Per	reel
Product Description	HellermannTyton’s Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.
Short Description	Spiralwrap Protective Sheathing, 0.5" Diameter, PA6, Natural, 100 ft/roll
Global Part Name	3N-PA6-NA

Length L (Imperial)	100.0
Length L (Metric)	30.48
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.375
Bundle Diameter Min (Metric)	9.52
Bundle Diameter Max (Imperial)	4.0
Bundle Diameter Max (Metric)	102.0
Diameter D (Imperial)	0.5
Diameter D (Metric)	12.7
Nominal Diameter (Imperial)	0.5
Nominal Diameter (Metric)	12.7
Wall Thickness WT (Imperial)	0.035
Wall Thickness WT (Metric)	0.89
Material	Polyamide 6 (PA6)
Material Shortcut	PA6

Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +250°F (-40°C to +121°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).