

1

2

3

4

5

6

7

8

Mark	Qty	Engineering Change Area

A


B

A

B

C

D



NOTE:

1. ELECTRICAL:

1.1.RATED VOLTAGE:50VAC/60 DC

1.2.RATED CURRENT:0.5A

1.3.CONTACT RESISTANCE:≤15mΩ

1.4.INSULATION RESISTANCE:≥100MΩ

1.5.RATED IMPULSE VOLTAGE:800V

2. ENVIRONMENTAL:

2.1.OPERATING TEMPERATURE: -25°C TO +85°C

2.2.PROTECTION GRADE:IP67,WHEN TIGHT LOCKED

2.3.POLLUTION DEGREE:3

3.CONTACT MATERIAL: BRASS NI PLATED UNDER GOLD PLATED

4.CONDUCTOR CROSS-SECTION:24-28AWG

5.CABLE RANGE:Ø5.6~8.8mm


6.CONFORM TO IEC 61076-2-109

* UNLESS OTHERWISE SPECIFIED
TOLERANCES ON DECIMAL IS:

X. ± 0.50 X° ± 2°

X.X ± 0.30

X.XX ± 0.20

All dimensions
are in mm

Material:											
Finishing:											
Phase Marking				Weight		Scale		拓宜(上海)工控电器设备有限公司 Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.			
						1:1					
P/N				61061507				Part Name: C12B-FSX-RM-8SCUP SH			
MD/CD								Rev. 01		Page: 1 OF 1	

1

2

3

4

5

6

7

8