




NOTE:

1.ELECTRICAL:

1.1.Rated Voltage:250V

1.2.Rated Current:4A

1.3.Contact Resistance:≤15mΩ

1.4.Insulation Resistance:≥100MΩ

1.5.Rated impulse voltage:2500V

2.ENVIRONMENTAL:

2.1.Operating Temperature: -25°C TO +85°C

2.2.Protection Grade:IP67,When Tight Locked

2.3.Pollution Degree:3

3.Contact Material: Brass NI Plated Under
Gold Flash Plated

4.Cable Range:22-20AWG


5.Conform to IEC 61076-2-101

* UNLESS OTHERWISE SPECIFIED
TOLERANCES ON DECIMAL IS:

X. ± 0.50 X° ± 2°

X.X ± 0.30

X.XX ± 0.20



All dimensions
are in mm

Material:

Finishing:

Phase Marking

Weight

Scale

P/N

61054607

MD/CD

Part Name:
C12B-FSD-FM1-4SCUP MX

Rev.

01

Page:

1 OF 1



拓宜(上海)工控电器设备有限公司
Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.