




Mark	Qty	Engineering Change Area

NOTE:

1.ELECTRICAL:


- 1.1.Rated Voltage:250V
- 1.2.Rated Current:4A
- 1.3.Contact Resistance:≤15mΩ
- 1.4.Insulation Resistance:≥100MΩ
- 1.5.Rated impulse voltage:2500V

2.ENVIRONMENTAL:


- 2.1.Operating Temperature: -25°C TO +85°C
- 2.2.Protection Grade:IP67,When Tight Locked
- 2.3.Pollution Degree:3

3.Contact Material: Brass NI Plated Under Gold Flash Plated

4.Conform to IEC 61076-2-101



RECOMMENDED PCB LAYOUT



PANEL CUT OUT

* UNLESS OTHERWISE SPECIFIED
TOLERANCES ON DECIMAL IS:

X.	± 0.50	X°	± 2°
X.X	± 0.30		
X.XX	± 0.20		

		Material:				
		Finishing:				
Signature Date	Created by	Checked by	Approved by	Phase Marking	Weight	Scale
						1:1
State	First Release	P/N	61050407	Part Name: C12B-FSD-RM1-4		
		MD/CD		Rev.	01	Page: 1 OF 1

TOPONELEC

拓宜(上海)工控电器设备有限公司
Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.