






NOTE:
 1. ELECTRICAL:
 1.1. RATED VOLTAGE: 50VAC/60 DC
 1.2. RATED CURRENT: 0.5A
 1.3. CONTACT RESISTANCE: $\leq 15\text{m}\Omega$
 1.4. INSULATION RESISTANCE: $\geq 100\text{M}\Omega$
 1.5. Rated impulse voltage: 800V
 2. ENVIRONMENTAL:
 2.1. OPERATING TEMPERATURE: -25°C TO +85°C
 2.2. PROTECTION GRADE: IP67, WHEN TIGHT LOCKED
 2.3. POLLUTION DEGREE: 3
 3. CONTACT MATERIAL: BRASS NI PLATED UNDER GOLD PLATED
 4. CONFORM TO IEC 61076-2-109

* UNLESS OTHERWISE SPECIFIED
 TOLERANCES ON DECIMAL IS:
 X. ± 0.50 X° $\pm 2^\circ$
 X.X ± 0.30
 X.XX ± 0.20

 All dimensions are in mm			Material:						
			Finishing:						
					Phase Marking		Weight		Scale
					1:1				
Created by								Part Name:	
Checked by				P/N		61058207		C12B-FSX-FM-8 MX SH	
Approved by								Rev.	
State		First Release		MD/CD				01	
								Page:	
								1 OF 1	

Mark	Qty	Engineering Change Area