

Specification Sheet

Part Number: 151-02459



Connector clip design to meet USCAR EWCAP-005-11 clip slot specifications.

Meets installation and extraction requirements of SAE/USCAR-2.

Versatile and robust fir tree design provides low insertion effort yet delivers exceptional retention strength in a 5mm hole and M6 threaded hole.

USCAR Connector Clip with Round Fir Tree, 11mm, 5.0 mm Dia and M6 Threaded Hole, PA66HIRHSUV, Black, 5000/ctn

Article Number	151-02459
----------------	-----------

Type	CC11FTM6
------	----------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	USCAR Connector Clip with Round Fir Tree, 11mm, 5.0 mm Dia and M6 Threaded Hole, PA66HIRHSUV, Black, 5000/ctn
-------------------	---

Global Part Name	CC11FTM6-PA66HIRHSUV-BK
------------------	-------------------------

Length L (Imperial)	0.98
---------------------	------

Length L (Metric)	24.9
-------------------	------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Variant	M6 Threaded Hole
---------	------------------

Width W (Imperial)	0.622
--------------------	-------

Width W (Metric)	15.8
------------------	------

Height H (Imperial)	0.814
---------------------	-------

Height H (Metric)	20.7
-------------------	------

Panel Thickness Min (Imperial)	0.05
--------------------------------	------

Panel Thickness Max (Imperial)	0.18
--------------------------------	------

Panel Thickness Min (Metric)	1.3
------------------------------	-----

Panel Thickness Max (Metric)	4.5
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.24
-------------------------------------	------

Mounting Hole Diameter D (Metric)	M6
-----------------------------------	----

Mounting Hole Diameter D Min (Imperial)	0.256
---	-------

Mounting Hole Diameter D Max (Imperial)	0.276
Mounting Hole Diameter D Max (Metric)	7.0
Disc Diameter (Metric)	17.5
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	5008
Package Quantity (Metric)	5000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)