







2		1	
REV	CONTENT	CHK	DATE
V0.0	CONTENT	LZW	23.03.27

NOTES:

1. Material: PA66 UL94V-0;
2. The surface shall not have material flowers, shrinkage, deformation, lack of material, distortion, color and other adverse phenomena;
3. Operating temperature: -40~+105℃



6	Card buckle	XXXXXX	1	STEEL	Zn Plated
5	SLIDER	XXXXXX	1	SPRING STEEL	Ni Plated
4	CLASP	XXXXXX	2	PA66 UL94V-0	SEE NOTE
3	COVER-TOP	XXXXXX	1	PA66 UL94V-0	SEE NOTE
2	HOUSING-RIGHT	XXXXXX	1	PA66 UL94V-0	SEE NOTE
1	HOUSING-LEFT	XXXXXX	1	PA66 UL94V-0	SEE NOTE
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	LZW	DATE	23.03.27	SIZE	A4 UNITS mm SHEET/OF 1 / 1
CHK.	DATE			SCALE	1:1
APP.	DATE			NAME	TPKT-02P-14-00
				DWGNO.	XXXX



拓宜(上海)工控电器设备有限公司
Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.

A	Total Pitch Tolerances in mm									Nominal dimension range in mm								$\perp$		$\equiv$	$-$	$//$				
	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	all	over 0 to 100	over 100 to 150	over 150	
	to 30	to 53	to 70	to 90	to 115	to 150	to 250	to 350	to 500	to 30	to 53	to 70	to 90	to 115	to 150	to 200	to 250	to 320	to 10				to 100	to 150	to 150	
	± 0.18	± 0.20	± 0.25	± 0.3	± 0.35	± 0.44	± 0.60	± 0.70	± 0.85	± 0.20	± 0.25	± 0.30	± 0.35	± 0.44	± 0.55	± 0.70	± 0.80	± 0.90	0.2	0.3		0.3	0.2	0.3	0.5	
6									5									4								