




A

B

C

D

A


B

C

D

NOTE:
1. ELECTRICAL:
1.1.RATED VOLTAGE:50VAC/60 DC
1.2.RATED CURRENT:0.5A
1.3.CONTACT RESISTANCE:≤15mΩ
1.4.INSULATION RESISTANCE:≥100MΩ
1.5.Rated impulse voltage:800V
2. ENVIRONMENTAL:
2.1.OPERATING TEMPERATURE: -25°C TO +85°C
2.2.PROTECTION GRADE:IP67,WHEN TIGHT LOCKED
2.3.POLLUTION DEGREE:3
3.CONTACT MATERIAL: BRASS NI PLATED UNDER GOLD PLATED
4.CONDUCTOR CROSS-SECTION:24-28AWG
5.CABLE RANGE:Ø5.6~8.8mm
6.CONFORM TO IEC 61076-2-109

* UNLESS OTHERWISE SPECIFIED
TOLERANCES ON DECIMAL IS:
X. ± 0.50 X° ± 2°
X.X ± 0.30
X.XX ± 0.20

 All dimensions are in mm	Material:				
				Finishing:	
	Signature	Date	Phase Marking	Weight	Scale
	Created by				1:1
Checked by			P/N	61060907	Part Name: C12B-FSX-FM-8SCUP MX SH
Approved by			MD/CD		Rev. 01
State		First Release			Page: 1 OF 1