


A-CODE FEMALE INTERFACE



PANEL CUT OUT

NOTE:

1. ELECTRICAL:

1.1.CONTACT RESISTANCE:≤15mΩ

1.2.INSULATION RESISTANCE:≥100MΩ

2. ENVIRONMENTAL:

2.1.OPERATING TEMPERATURE: -25°C TO +85°C

2.2..PROTECTION GRADE:IP67,WHEN TIGHT LOCKED

2.3.POLLUTION DEGREE:3

3.CONTACT MATERIAL: BRASS NI PLATED UNDER GOLD PLATED

4.CONFORM TO IEC 61076-2-101


* UNLESS OTHERWISE SPECIFIED
TOLERANCES ON DECIMAL IS:

X. ± 0.50 X° ± 2°


X.X ± 0.30

X.XX ± 0.20

POLE	03	04	05	06	07	08
CONDUCTOR CROSS-SECTION	20~24AWG 0.5~0.25mm ²	20~24AWG 0.5~0.25mm ²	20~24AWG 0.5~0.25mm ²	24AWG 0.25mm ²	24AWG 0.25mm ²	24AWG 0.25mm ²
RATED VOLTAGE	250V	250V	60V	30V	30V	30V
RATED CURRENT	4A	4A	4A	2A	2A	2A
RATED IMPULSE VOLTAGE	2.5KV	2.5KV	1.5KV	0.8KV	0.8KV	0.8KV



PANEL HOUSING
T=1.0~3.0



All dimensions
are in mm

Material:

Finishing:

Phase Marking

Weight

Scale



拓宜(上海)工控电器设备有限公司
Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.

Part Name:
C12B-FSA-FM1-8SCUP MX

Rev.
01

Page:
1 OF 1

Created by

Signature

Date

Checked by

Approved by

State

First Release

P/N

61037807

MD/CD