



Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:20A AC/DC

额定电流: 20A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-40°C-+125°C

温度范围: -40°C-+125°C

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

K 838100 T M - B SN
① ② ③ ④ ⑤ ⑥

1.K: XKBTEK-Car Connector

2.XKB Series No

3.Category:T-Terminal

4.Special No:M-Male Terminal

5.Material:B-Brass

6.Plating:SN-Plated Tin

K838100TM-BSN	Brass	AWG#22~16	K838100HF
PART NO	Material	Wire Range	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 8.38mm Automobile connector
DWN	VIEW:	PART NO.: K838100TM-BSN
CHKD	UNIT: mm/in	DWG NO.: X-K838100TM-BSN
APPD	SIZE: A4	WEIGHT SHEET REVISION



XKB INDUSTRIAL PRECISION CO.,LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES