





REV	CONTENT	CHK	DATE
V0.0	CONTENT	YL	22.11.21



SECTION A-A



**Electrical :**

	UL	IEC
1.Rated Voltage :	300V	250V
2.Rated Current :	8A	7A
3.Torque Value :	M2 ,1.77Lb.in	M2, 0.2N.m
4.Wire Range:	28-16AWG	0.5-1.5mm <sup>2</sup>
5.Stripping Length :	6-7mm	
6.Withstanding Voltage :	AC1600V/1Min.	
7.Operating Temperature :	-40°C~+105°C	
8.RoHS Compliance		
9."★" is the key quality control point		

15ETYK - 3.81 - XXP - X X - 100

① ② ③ ④ ⑤ ⑥

- ① Series NO.      ④ 1 Single Pitch  
                                    2 Double Pitch
- ② Pitch                      ⑤ Color: 1 Grey  
  2 Blue  
  3 Black  
  4 Green  
  5 Orange  
  6 Red  
  7 Transparent  
  8 Yellow  
  9 White
- ③ Poles  
  02 02Contacts  
  03 03Contacts  
  24 24Contacts

⑥ Customer Request: 100--Standard  
(Cooperate with tight)

5	SCREW	XX	P	STEEL	Zn Plated
4	BLOCK	XX	P	BRASS	Ni Plated
3	CLAMP	XX	P	PHOSPHOR BRONZE	Ni Plated
2	COVER	XX	1	PA66 UL94V-0	SEE NOTE
1	HOUSING	XX	1	PA66 UL94V-0	SEE NOTE
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	YL	DATE	22.11.21	SIZE	A4 UNITS mm SHEET/OF 1 / 1
CHK.	DATE		SCALE	1:1	
APP.	DATE			NAME 15ETYK-3.81-XXP-XX-100	
<b>拓宜(上海)工控电器设备有限公司</b> Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.				DWGNO. XXXX	

Total Pitch Tolerances in mm													Nominal dimension range in mm												⊥	=	-	//
over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	0	over	over	over	
0	30	53	70	90	115	150	250	350	0	30	53	70	90	115	150	200	250	0	over	over	over	over	0	100	150	0	100	150
to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to		
30	53	70	90	115	150	250	350	500	30	53	70	90	115	150	200	250	320	10	all	to	to	to	to	to	to	to		
±0.18	±0.20	±0.25	±0.3	±0.35	±0.44	±0.60	±0.70	±0.85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2	0.3	0.3	0.2	0.3	0.5					