



Material :

- (a) Cover : PA66(UL94V-0)
- (b) Contact : Phosphor Bronze
- (c) Cage : Brass , Ni Plated
- (d) Housing : PA66(UL94V-0)
- (e) Screws : Steel , Cr³⁺Zn Plated

Electrical :



- 1.Rated Voltage : 300V
- 2.Rated Current : 15A
- 3.Torque Value : M2.5 , 3.54Lb.in
- 4.Wire Range: 28-12AWG
- 5.Stripping Length : 7-8mm
- 6.Withstanding Voltage : AC1600V/1Min.
- 7.Operating Temperature : -40 °C~+105 °C
- 8.RoHS Compliance
- 9.Safety Approval :
- 10.Undimensioned Tolerances:

Pitch Range In mm			Nominal Dimension Range In mm						
≤6	6 ~ 10	10 ~ 24	≤30	30 ~ 60	60 ~ 100	100 ~ 150	>150	0.05/10	
±0.10	±0.15	±0.25	±0.20	±0.30	±0.50	±0.70	±1.00	±0.1°	



2ETYKA - 5.08 - XXP - 1 3 - 100

- ① Series No.
- ② Pitch
- ③ Poles
- ④ 1 Single Pitch
2 Double Pitch
- ⑤ Color: 1 Grey
2 Blue
3 Black
4 Green(Standard For AH)
5 Orange
6 Red
7 Transparent
8 Yellow
9 White
- ⑥ Customer Request:
100--Standard M2.5



DETACHED LISTS			拓宜(上海)工控电器设备有限公司 Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD			
	APPD: 9/16/16 '		PART NO. 2ETYKA-5.08-XXP-13-100			
	CHKD: 9/15/16 '					
	DRFT: 9/14/16 '		DRAWING NO.		REV	1
	 THIRD ANGLE PROJECTION				SHEET	1/1
				DO NOT SCALE DRAWING	SCALE	1/1