






REV	CONTENT	CHK	DATE
V0.0	CONTENT	YL	22.11.19

Electrical :

- 1.Rated Voltage : 300V UL 320V IEC
2.Rated Current : 15A 20A
3.Withstanding Voltage : AC1600V/1Min;
4.Operating Temperature : -40°C~+105°C;
5. RoHS Compliance;
6.Safty Approval : 
7."★" is the key quality control point.

2ETYRM - 5.08 -XXP - X X - 100

① ② ③ ④ ⑤ ⑥

① Sereies No. ④ 1 Single Pitch
2 Double Pitch

② Pitch

⑤ Color: 1 Grey
2 Blue
3 Black
4 Green
5 Orange
6 Red
7 Transparent
8 Yellow
9 White

③ Poles
02 02Contacts
03 03Contacts
...
24 24Contacts

⑥ Customer Request: 100--Standard

A	Total Pitch Tolerances in mm									Nominal dimension range in mm									$\perp$		$\equiv$	$-$		$//$					
	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	all	over 0	over 100	over 150				
	to 30	to 53	to 70	to 90	to 115	to 150	to 250	to 350	to 500	to 30	to 53	to 70	to 90	to 115	to 150	to 200	to 250	to 320	to 10				to 100	to 150	to 150				
	± 0.18	± 0.20	± 0.25	± 0.3	± 0.35	± 0.44	± 0.60	± 0.70	± 0.85	± 0.20	± 0.25	± 0.30	± 0.35	± 0.44	± 0.55	± 0.70	± 0.80	± 0.90	0.2	0.3	0.3	0.3	0.2	0.3	0.5				
6										5										4									

3	NUT	XX	2	BRASS	--
2	PIN	XX	P	BRASS	Tin Plated
1	HOUSING	XX	1	PA66 UL94V-0	GREEN
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	YL	DATE	22.11.19	SIZE	A4 UNITS mm SHEET/OF 1 / 1
CHK.	DATE			SCALE	1:1
APP.	DATE				
 拓宜(上海)工控电器设备有限公司 Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.				NAME	2ETYRM-5.08-XXP-XX-100
				DWGNO.	XXXXX