




REV	CONTENT	CHK	DATE
V0.0	CONTENT	YL	22.11.19

Electrical :

- 1.Rated Voltage : 300V
2.Rated Current : 15A
3.Withstanding Voltage : AC1600V/1Min;
4.Operating Temperature : -40°C~+105°C;
5. RoHS Compliance;
6.Safty Approval :
7."★" is the key quality control point.

2ETYRC - 5.08 -XXP - X X - 100
① ② ③ ④ ⑤ ⑥

- ① Sereies No. ④ 1 Single Pitch
2 Double Pitch
② Pitch ⑤ Color: 1 Grey
2 Blue
3 Black
4 Green
5 Orange
6 Red
7 Transparent
8 Yellow
9 White
⑥ Customer Request: 100--Standard

2	PIN	XX	P	BRASS	Tin Plated
1	HOUSING	XX	1	PA66 UL94V-0	GREEN
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	YL	DATE	22.11.19	SIZE	A4 UNITS mm SHEET/OF 1 / 1
CHK.	DATE		SCALE	1:1	
APP.	DATE		NAME	2ETYRC-5.08-XXP-XX-100	
拓宜(上海)工控电器设备有限公司 Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.			DWNGO.	XXXX	