



项目	规格
额定负荷	DC 12V 50mA
绝缘电阻	100MΩ min. 100v Dc
耐压强度	AC250V 50HZ 1mi n
电器寿命	50000次
环境温度	-25-70℃
相对湿度	(40℃) ≤95%
接触电阻	50mΩ max
行程	0.20±0.05mm
动作力	260gf±20gf

PAPT NO	TS1109-X-X	
Operating Force	160 : 160gf ; 260 : 260gf	
Height	38 : 3.8mm	65 : 6.5mm
	43 : 4.3mm	70 : 7.0mm
	45 : 4.5mm	75 : 7.5mm
	50 : 5.0mm	80 : 8.0mm
	55 : 5.5mm	85 : 8.5mm
	60 : 6.0mm	90 : 9.0mm

					new		2015/5/3		A		瀚源	
					ECN BO.		DESCRIPTION.		DATE.		REV.	
					DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1	
E	盖板	铁皮	1	镀锡	Mikey	Tom	Jerry	PART NAME	TS1109-X-X	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X.	±0.25
D	按钮	PPA	1					MODEL NAME	TS1109-X-X		X.x	±0.20
C	簧片	不锈钢覆银	1								X.xx	±0.15
B	底座	PPA	1							ANGULAIR	±3	
A	卡件	黄铜	1	镀银								
序号	名称	材料	数量	备注				3RD ANGLE PROJ	HanElectricity Co.,LTD		FILE.NO.	