




电路图

|                 |                           |               |
|-----------------|---------------------------|---------------|
| PAPT NO         | TC1104-X-X                |               |
| Operating Force | 160 : 160gf ; 260 : 260gf |               |
| Height          | 43 : 4.3mm                | 75 : 7.5mm    |
|                 | 45 : 4.5mm                | 80 : 8.0mm    |
|                 | 50 : 5.0mm                | 85 : 8.5mm    |
|                 | 55 : 5.5mm                | 90 : 9.0mm    |
|                 | 60 : 6.0mm                | 95 : 9.5mm    |
|                 | 65 : 6.5mm                | 100 : 10.0mm  |
|                 | 70 : 7.0mm                | 10.5mm...19mm |

|          |         |              |                |                        |  |                                          |            |            |  |
|----------|---------|--------------|----------------|------------------------|--|------------------------------------------|------------|------------|--|
|          |         | new          |                | 2015/5/3               |  | A                                        |            | 瀚源         |  |
| ECN BO.  |         | DESCRIPTION. |                | DATE.                  |  | REV.                                     |            |            |  |
| DESIGNED | CHECKED | APPROVAL     | DRAWING NUMBER |                        |  |                                          | SCALT: 1/2 | SCALE: 3:1 |  |
| Mikey    | Tom     | Jerry        | PART NAME      | TC1104-X-X             |  | UNLESS OTHERWISE<br>SPECIFIED,TOLERANCE: | X.         | ±0.25      |  |
|          |         |              | MODEL NAME     | TC1104-X-X             |  |                                          | X.x        | ±0.20      |  |
|          |         |              | 3RD ANGLE PROJ | HanElectricity Co.,LTD |  |                                          | X.xx       | ±0.15      |  |
|          |         |              |                |                        |  |                                          | ANGULAIR   | ±3         |  |
|          |         |              |                |                        |  |                                          | FILE.NO.   |            |  |