


Ass'y High(H)	Plastic High	
	Male (H1)	Female (H2)
8.00	6.90	6.00
10.00	8.90	6.00



SPECIFICATIONS

PERFORMANCE

Current Rating (信号端子): 0.5A
Current Rating (电源端子): 5A
Contact Resistance: 80mΩ Max
Insulation Resistance: 500MΩ Min
Withstand Volt: 200V AC/minute
Oprating Temperature: -40°C to +105°C

Material

Contact: Phosphor Bronze, 3u" MIN Gold Plated In Contact Area,
Gold Flash Plated In Solder Area,
50u"~240u" Nickel Underplated Over all.
Ground: Brass, 80u" Min Matte Tin Plated Over
50u" Min Nickel Underplated Over all.
Housing: LCP Black, UL94V0
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

PIN	A	B	C	D	E
30 Pin	22.00	8.30	7.00	11.80	20.00
50 Pin	27.00	13.30	12.00	16.80	25.00
60 Pin	29.50	15.70	14.50	19.30	27.50
80 Pin	34.50	20.70	19.50	24.30	32.50
100 Pin	39.50	25.70	24.50	29.30	37.50
120 Pin	44.50	30.70	29.50	34.30	42.50

Ordering Information

HC-PBB23L - NDS - 0.5V - ** - 01

No. of Pins	Nature DS-Female	PITCH	Contact Plating
30~120Pin	(H)	0.5V±0.5mm	G2:2u" Gold
30~30Pin			S0:1u" Gold/Tin
50~50Pin			S1:3u" Gold/Tin
.....			S2:5u" Gold/Tin
			S3:10u" Gold/Tin
			S4:15u" Gold/Tin
			S5:30u" Gold/Tin

			GENERAL TOLERANCE	制 图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审 核 CHECK				
			X. X ±0.30	批 准 APPROVAL	产品名称 TITLE	BTB 0.5 高频大电流 浮动式 H6.0 贴片母座	版 本 REV.	A
			X. XX ±0.20	比 例 SCALE	产品料号 PART NO.	HC-PBB23L-NDS-0.5V-XX-01	单 位 UNITS	mm
			X. XXX ±0.10	投 影 Projection				
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°		材 料 MATERIAL	页 次 SHEET 1/1		