



REV	ECN NO.	APPD
A	HR-22-0062	PRIDJM




规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.2±0.1mm



CIRCUIT DIAGRAM

回路图



RECOMMENDED P.C.B. LAYOUT

安装尺寸图

PRODUCT NO.: 1TS008D-***0-***0A1-CT

轻触开关

3X4立式小龟系列

外形:

操作力度:

250=250gf

手感:

0=常規

材料:

0=初始材料

1=新增材料

依次增加

编带
非编带, 不启用

产品高度 (H):

200=2.0mm

250=2.5mm

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
6	ACTUATOR	1	LCP	grey
5	COVER	1	SUS	naturalcolor
4	FILM	1	PI	Yellow
3	DOME	2	SUS301	Ag-PLATED
2	HOUSING	1	LCP	grey
1	TERMINAL	1	CS191	Ag-PLATED

UNITS	NAME(INTENDED USE)	NAME(INTENDED USE)
MM	3X4 SERIES	3X4 SERIES
MAT'L	TACT SWITCH	TACT SWITCH
FINISH	PART NO.(INTENDED USE)	PART NO.(INTENDED USE)
	1TS008D-2500-2000A1-CT	1TS008D-2500-2000A1-CT

APPD:	ZD 8/10/2022	DWG NO.:	1TS008D-2500-2000A1-CT
CHKD:	M.H.L 8/10/2022	TITLE:	PRODUCT DRAWING
DR:	Z.M.Cal 8/10/2022	SCALE	SHEET 1/1
		REV.	A

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT PREVIOUS WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.