







RECOMMENDED P.C.B. LAYOUT


安装尺寸图

规格 Specifications	
额定负荷 Rating	DC 12V/20mA
接触电阻 Contact Resistance	100mΩ max
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S
操作力 Operation force	250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.15±0.05mm



CIRCUIT DIAGRAM

回路图



PRODUCT NO.: 1TS001G****-***** A1 - CT

轻触开关
4x4系列
外形:
按钮颜色:
底座颜色:
盖板颜色:

材料:
0=初始材料
1=新增材料
依次增加

操作力度:
160=160gf
180=180gf
260=260gf

初始颜色, 则不启用

手感:

0=常规(弹片)

1=大手感(弹片)

2=小手感(弹片)

3=特殊手感(弹片)

产品高度(H):

150=1.50mm

160=1.60mm

170=1.70mm

200=2.00mm

编带
非编带, 不启用

X. ± 0.2	X' ± 3'	UNITS	PART NAME	QUANTITY	MATERIAL	FINISH
X ± 0.1	X' ± 2'	MATL	NAME(INTENDED USE)	4X4	HON YUAN	HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.
.XX ± 0.05	.XX' ± 1'	FINISH	PART NO.(INTENDED USE)	1TS001G-2500-1700A1	TITLE:	PRODUCT DRAWING
.XXX ± 0.03	.XXX' ± 0.5'	Q'TY	APPD:	W.P.Lu 2016.11.30	DWG NO.:	1TS001G-2500-1700A1-CT
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.		CHKD:	S.L.Li 2016.11.30	DR:	Y.Y.Chen 2016.11.30	SCALE SHEET REV.
				10/1	1/1	A