




RECOMMENDED P.C.B. LAYOUT

安装尺寸图



CIRCUIT DIAGRAM  
回路图



规格 Specifications

额定负荷 Rating	DC 12V/20mA
接触电阻 Contact Resistance	100mΩ max
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min
抗电强度 Dielectric strength	AC250V/(50-60HZ) 60S
操作力 Operation force	250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.15±0.05mm

PRODUCT NO.: 1TS001G\*\*\*\*-\*\*\*\*-\*\*\*\* A1 - CT

- 轻触开关
- 4x4系列
- 外形:
- 按钮颜色:
- 底座颜色:
- 盖板颜色:
- 操作力度:
  - 160=160gf
  - 180=180gf
  - 260=260gf
- 手感:
  - 0=常规(弹片)
  - 1=大手感(弹片)
  - 2=小手感(弹片)
  - 3=特殊手感(弹片)
- 产品高度(H):
  - 150=1.50mm
  - 160=1.60mm
  - 170=1.70mm
  - 200=2.00mm
- 材料:
  - 0=初始材料
  - 1=新增材料
  - 依次增加
- 编带
- 非编带, 不启用

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
6	HOUSING	1	LCP	GREY
5	TERMINAL	1	C5191	Ag-plating(0.2um Min)
4	DOME	1	SUS301	Ag-plating(0.3um Min)
3	PE-FILE	1	PI	YELLOW
2	COVER	1	SUS	NATURAL COLOR
1	ACTUATOR	1	C2680/PBA	YELLOW/WHITE

UNITS	MM	NAME(INTENDED USE)	4X4	HON YUAN
X. ± 0.2	X' ± 3'	TACT SWITCH		HON YUAN PRECISION IND. CO.,LTD.
X ± 0.1	X' ± 2'	PART NO.(INTENDED USE)		SHENZHEN, CHINA.
.XX ± 0.05	.XX' ± 1'	1TS001G-2500-1600A1		PRODUCT DRAWING
.XXX ± 0.03	.XXX' ± 0.5'	APPD: W.P.Lu 2016.11.30		DWG NO.: 1TS001G-2500-1600A1-CT
		CHKD: S.L.Li 2016.11.30		SCALE SHEET REV.
		DR: Y.Y.Chen 2016.11.30		10/1 1/1 A

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.