





Technical Index:
 1. Temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
 2. Rated voltage: 200V DC/AC(rms).
 3. Rated current: 2.0A.
 4. Contact resistance: $\leq 25\text{m}\Omega$.
 5. Withstanding voltage: 500V AC/minute.
 6. Insulation resistance: $\geq 1000\text{M}\Omega$.



Part No	Pin	A	B
WAFER-HY2.0-2PWZ-R62	2	2.00	6.00
WAFER-HY2.0-3PWZ-R62	3	4.00	8.00
WAFER-HY2.0-4PWZ-R62	4	6.00	10.00
WAFER-HY2.0-5PWZ-R62	5	8.00	12.00
WAFER-HY2.0-6PWZ-R62	6	10.00	14.00
WAFER-HY2.0-7PWZ-R62	7	12.00	16.00
WAFER-HY2.0-8PWZ-R62	8	14.00	18.00
WAFER-HY2.0-9PWZ-R62	9	16.00	20.00
WAFER-HY2.0-10PWZ-R62	10	18.00	22.00
WAFER-HY2.0-11PWZ-R62	11	20.00	24.00
WAFER-HY2.0-12PWZ-R62	12	22.00	26.00
WAFER-HY2.0-13PWZ-R62	13	24.00	28.00
WAFER-HY2.0-14PWZ-R62	14	26.00	30.00
WAFER-HY2.0-15PWZ-R62	15	28.00	32.00
WAFER-HY2.0-16PWZ-R62	16	30.00	34.00
WAFER-HY2.0-17PWZ-R62	17	32.00	36.00
WAFER-HY2.0-18PWZ-R62	18	34.00	38.00
WAFER-HY2.0-19PWZ-R62	19	36.00	40.00
WAFER-HY2.0-20PWZ-R62	20	38.00	42.00



序号	品名	材质
1	HY2.0 弯针 胶芯	PA66 UL94V-2 Red
2	HY2.0 弯针 端子	Copper Alloy/ Tin Plating



适用线路板(PCB LAYOUT)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: HY2.0 弯针带扣
DECIMALS:	ANGLES:		PAR WAFER-HY2.0-NPWZ-R62
X.:±0.50	X'::±5°		DWN
.X.:±0.20	X.X'::±3°		CHKD
.XX.:±0.10	X.XX'::±1°	APVD	SCALE:1:1 UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1 REV:A