








规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.25±0.1mm

RECOMMENDED P.C.B. LAYOUT

安装尺寸图



CIRCUIT DIAGRAM

回路图

5	COVER	1	BRASS	Ni-PLATED
4	ACTUATOR	1	PPA	BLACK
3	DOME	1	Stainless Steel/Ag	Ag-PLATED
2	TERMINAL	1	BRASS	Ag-PLATED
1	HOUSING	1	PPA	BLACK
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH

X. ± 0.3	X' ± 3'	UNITS	NAME(INTENDED USE)	HON YUAN
X ± 0.2	X' ± 2'	MAT'L	6X6 SERIES TACT SWITCH	HON YUAN PRECISION IND. CO.,LTD.
.XX ± 0.1	.XX' ± 1'	FINISH	PART NO.(INTENDED USE)	SHENZHEN, CHINA.
.XXX ± 0.05	.XXX' ± 0.5'		1TS005F-2500-4301A2	PRODUCT DRAWING

APPD: W.P.Lu 2018.3.31	DWG NO.: 1TS005F-2500-4301A2-CT
CHKD: S.L.Li 2018.3.31	
DR: Y.Y.Chen 2018.3.31	

PRODUCT NO.: 1TS 005F****-4300A2 - CT

轻触开关

系列:

外形:

按钮颜色:

底座颜色:

盖板颜色:

操作力度: 250±250gf

手感: 0=常闭(弹片)

材质: 0=初始材质 1=新增材质 依次增加

产品高度(H): 430=4.3mm

非编带

初始颜色, 则不启用

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED OR COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN

SCALE SHEET REV. 10/1 1/2 A