








Technical Index:

- 1.The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)
- 2.Lock Configuration: 2 to 3Pin is 1, ≥ 4 Pin is 2
- 3.Temperature range: $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 4.Rated voltage: 125V.AC/DC.
- 5.Contact resistance: $\leq 0.02\Omega$.
- 6.Insulation resistance: $\geq 100\text{M}\Omega$



适用线路板(PCB LAYOUT)



Part No	Pin	A	B	C
XY-MX1.25-2A21-YT	2	1.25	3.20	4.30
XY-MX1.25-3A21-YT	3	2.50	4.45	5.55
XY-MX1.25-4A21-YT	4	3.75	5.70	6.80
XY-MX1.25-5A21-YT	5	5.00	6.95	8.05
XY-MX1.25-6A21-YT	6	6.25	8.20	9.30
XY-MX1.25-7A21-YT	7	7.50	9.45	10.55
XY-MX1.25-8A21-YT	8	8.75	10.70	11.80
XY-MX1.25-9A21-YT	9	10.00	11.95	13.05
XY-MX1.25-10A21-YT	10	11.25	13.20	14.30
XY-MX1.25-11A21-YT	11	12.50	14.45	15.55
XY-MX1.25-12A21-YT	12	13.75	15.70	16.80
XY-MX1.25-13A21-YT	13	15.00	16.95	18.05
XY-MX1.25-14A21-YT	14	16.25	18.20	19.30
XY-MX1.25-15A21-YT	15	17.50	19.45	20.55
XY-MX1.25-16A21-YT	16	18.75	20.70	21.80
XY-MX1.25-17A21-YT	17	20.00	21.95	23.05
XY-MX1.25-18A21-YT	18	21.25	23.20	24.30
XY-MX1.25-19A21-YT	19	22.50	24.45	25.55
XY-MX1.25-20A21-YT	20	23.75	25.70	26.80

序号	品名	材质
1	底座Wafer	PA66 黄色
2	端子Contact	铜合金/镀锡

DIMENSION IN mm		厦门市辛译精密电子有限公司					
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyconn Electronics Co.,Ltd					
.X±0.35	X.*±5°	APR.	Alex	TITLE: WAFER 1.25 90° DIP 黄色			
.XX±0.25	.X.*±3°	CHK.	Jack	DWG NO. XY-MX1.25-NA21-YT			
.XXX±0.15	.XX.*±1°	DRA.	Can	PROJ.		CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1/1	REV. A