








REV	ECN NO.	APPD
A	HC-20-0100	ZO
B	HC-24-0023	ZO

规格 Specifications


额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	500mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160±30gf
寿命试验 Operating Life	200,000 cycles
行程 Travels	0.12±0.05mm

LAND PATTERN PLAN
印刷电路板焊盘参考图

PRODUCT NO.: 1TS032A-1600-2903-CT



ITEM	P/N	PART NAME	Q'TY	MAT'L	FINISH	SPECIFICATION	REMARK
8		STEM	1		POLYAMIDE		BLACK
7		METAL COVER	1		BRASS		Ag-PLATED
6		PLASTIC COVER	1		POLYAMIDE		BLACK
5		KNOB	1		POLYAMIDE		BLACK
4		FILM	1		POLYAMIDE		WHITE
3		DOME	3		SUS301		Ag-PLATED
2		HOUSING	1		POLYAMIDE		BLACK
1		TERMINAL	1		PHOSPHOR BRONZE		Ag-PLATED
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH			

ITEM		P/N	PART NAME	Q'TY	MAT'L	FINISH	SPECIFICATION		REMARK
X. ± 0.2		X'. ± 3'	UNITS	MM	NAME(INTENDED USE) 2X3 SIDE PUSH SERIES LASER WATERPROOF		HON YUAN HON YUAN PRECISION IND. CO.,LTD SHENZHEN, CHINA.		
.X ± 0.1		.X' ± 2'	MAT'L						
.XX ± 0.05		.XX' ± 1'		PART NO.(INTENDED USE)		TITLE:			
.XXX ± 0.03		.XXX' ± 0.5'	FINISH	1TS032A-1600-2903-CT		PRODUCT DRAWNG			
THESE DIMENSIONS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.				Q'TY	APPD:		DWG NO.:		
					W.P.LU 2024-01-16		1TS032A-1600-2903-CT		
					CHKD: S.L.LI 2024-01-16				
					DR: Z.M.Cai 2024-01-16				
					SCALE	SHEET	REV.		
					25/1	1/1	B		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED OR COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.

HON YUAN
HON YUAN PRECISION IND. CO., LTD.
SHENZHEN, CHINA.

PRODUCT DRAWING