








Technical Index:

- 1.The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)
- 2.Lock Configuration: 2 to 3Pin is 1, ≥ 4 Pin is 2
- 3.Temperature range: $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 4.Rated voltage: 125V.AC/DC.
- 5.Contact resistance: $\leq 0.02\Omega$.
- 6.Insulation resistance: $\geq 100\text{M}\Omega$



适用线路板(PCB LAYOUT)



Part No	Pin	A	B	C
XY-MX1.25-2A21-R	2	1.25	3.20	4.30
XY-MX1.25-3A21-R	3	2.50	4.45	5.55
XY-MX1.25-4A21-R	4	3.75	5.70	6.80
XY-MX1.25-5A21-R	5	5.00	6.95	8.05
XY-MX1.25-6A21-R	6	6.25	8.20	9.30
XY-MX1.25-7A21-R	7	7.50	9.45	10.55
XY-MX1.25-8A21-R	8	8.75	10.70	11.80
XY-MX1.25-9A21-R	9	10.00	11.95	13.05
XY-MX1.25-10A21-R	10	11.25	13.20	14.30
XY-MX1.25-11A21-R	11	12.50	14.45	15.55
XY-MX1.25-12A21-R	12	13.75	15.70	16.80
XY-MX1.25-13A21-R	13	15.00	16.95	18.05
XY-MX1.25-14A21-R	14	16.25	18.20	19.30
XY-MX1.25-15A21-R	15	17.50	19.45	20.55
XY-MX1.25-16A21-R	16	18.75	20.70	21.80
XY-MX1.25-17A21-R	17	20.00	21.95	23.05
XY-MX1.25-18A21-R	18	21.25	23.20	24.30
XY-MX1.25-19A21-R	19	22.50	24.45	25.55
XY-MX1.25-20A21-R	20	23.75	25.70	26.80

序号	品名	材质
1	底座Wafer	PA66 红色
2	端子Contact	铜合金/镀锡

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: WAFER 1.25 90° DIP 红色	
.X ± 0.35	X.* $\pm 5^{\circ}$	CHK.	Jack	DWG NO. XY-MX1.25-NA21-R	
.XX ± 0.25	.X.* $\pm 3^{\circ}$	DRA.	Can	PROJ. CUSTOMER DRAWING	
.XXX ± 0.15	.XX.* $\pm 1^{\circ}$	SIZE A4	SCALE 1:1	SHEET 1/1	REV. A