




REV	ECN NO.	APPD
A	HG-20-0050	PROJOM

规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60Hz) 60S min.
操作力 Operation force	160±40gf
寿命试验 Operating Life	50,000 cycles
行程 Travels	0.25±0.1mm

CIRCUIT DIAGRAM
回路图

PRODUCT NO.: 1TS002G***-***** A1 - CT

编带
非编带, 不启用轻触开关
3X6系列

外形:

A=插脚

B=贴片

C=贴片带柱

G=侧按带柱

材质:
0=初始材质
1=新增材质
依次增加产品高度 (H):
350=3.5mm按钮颜色:
底座颜色:
盖板颜色:

操作力度:

手感:

初始颜色

则不启用

160=160gf
260=260gf0=常规
1=大手感
2=小手感
3=特殊手感

安装参考图

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	ACTUATOR	1	PPA	Block
4	COVER	1	BRASS	Ag-PLATED
3	DOME	1	STAINLESS STEEL	Ag-PLATED
2	HOUSING	1	LCP	White
1	TERMINAL	2	BRASS	Ag-PLATED

NAME(INTENDED USE)	HON YUAN
3X6 SMT SERIES TACT SWITCH	HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.
PART NO.(INTENDED USE)	PRODUCT DRAWING
1TS002G-1600-3500A1	

UNITS	MM
X. ± 0.3	X' ± 3'
X. ± 0.2	X' ± 2'
.XX ± 0.1	.XX' ± 1'
.XXX ± 0.05	.XXX' ± 0.5'

Q'TY	DR:	SCALE	SHEET	REV.
	Y.Y.Chen 2020.07.01	10/1	1/1	A

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.