







REV.	Q'TY	ECN. NO.	APR.	DATE

Technical Index:

- 1.The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)
- 2.Lock Configuration: 2 to 3Pin is 1, ≥4Pin is 2
- 3.Temperature range: -25°C~+85°C.
- 4.Rated voltage: 125V.AC/DC.
- 5.Contact resistance: ≤0.02Ω.
- 6.Insulation resistance: ≥100MΩ

Part No	Pin	A	B	C
XY-MX1.25-2A11-YT	2	1.25	3.20	4.30
XY-MX1.25-3A11-YT	3	2.50	4.45	5.55
XY-MX1.25-4A11-YT	4	3.75	5.70	6.80
XY-MX1.25-5A11-YT	5	5.00	6.95	8.05
XY-MX1.25-6A11-YT	6	6.25	8.20	9.30
XY-MX1.25-7A11-YT	7	7.50	9.45	10.55
XY-MX1.25-8A11-YT	8	8.75	10.70	11.80
XY-MX1.25-9A11-YT	9	10.00	11.95	13.05
XY-MX1.25-10A11-YT	10	11.25	13.20	14.30
XY-MX1.25-11A11-YT	11	12.50	14.45	15.55
XY-MX1.25-12A11-YT	12	13.75	15.70	16.80
XY-MX1.25-13A11-YT	13	15.00	16.95	18.05
XY-MX1.25-14A11-YT	14	16.25	18.20	19.30
XY-MX1.25-15A11-YT	15	17.50	19.45	20.55
XY-MX1.25-16A11-YT	16	18.75	20.70	21.80
XY-MX1.25-17A11-YT	17	20.00	21.95	23.05
XY-MX1.25-18A11-YT	18	21.25	23.20	24.30
XY-MX1.25-19A11-YT	19	22.50	24.45	25.55
XY-MX1.25-20A11-YT	20	23.75	25.70	26.80



序号	品名	材质
1	基座Wafer	PA66 黄色
2	端子Contact	铜合金/镀锡

DIMENSION IN mm		<b>厦门市辛译精密电子有限公司</b> <b>Xiamen XinYi Xyecom Electronics Co.,Ltd</b>		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
.X±0.35	X.*±5°	APR.	Alex	TITLE: WAFER 1.25 180° DIP 黄色
.XX±0.25	.X.*±3°	CHK.	Jack	DWG NO. XY-MX1.25-NA11-YT
.XXX±0.15	.XX.*±1°	DRA.	Can	PROJ.  CUSTOMER DRAWING
		SIZE A4	SCALE 1:1	SHEET 1/1 REV. A