









规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160±40gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.12±0.1mm



ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	ACTUATOR	1	LCP	
4	COVER	1	SUS	
3	DOME	2	SUS	Ag-PLATED
2	HOUSING	1	LCP	
1	TERMINAL	1	C5191	Ag-PLATED

PRODUCT NO.: 1TS 029B-----A7 - CT

轻触开关

外形:

按钮颜色:

底座颜色:

盖板颜色:

操作力度:

初始颜色, 则不启用

手感:

材料:

产品高度 (H):

非编带

100=100gf

160=160gf

180=180gf

250=250gf

CIRCUIT DIAGRAM

回路图

HON YUAN

HON YUAN PRECISION IND. CO.,LTD.
SHENZHEN, CHINA.

TITLE:

PRODUCT DRAWING

DWG NO.: 1TS029B-1600-1400A7-CT

CHKD: S.L.Li 2024/1/10

DR: K.DING 2024/1/10

SCALE SHEET REV. 10/1 1/1 A