







| REV | ECN NO.    | APPD    |
|-----|------------|---------|
| A   | HR-17-0015 | PRJ0J0M |

规格 Specifications

|                            |                          |
|----------------------------|--------------------------|
| 额定负荷 Rating                | DC 12V/50mA              |
| 接触电阻 Contact Resistance    | 100mΩ max.               |
| 绝缘电阻 Insulation resistance | DC100V 60S 100MΩ min.    |
| 抗电强度 Dielectric strength   | AC250V(50~60HZ) 60S min. |
| 操作力 Operation force        | 250±50gf                 |
| 寿命试验 Operating Life        | 100,000 cycles           |
| 行程 Travels                 | 0.25±0.1mm               |



CIRCUIT DIAGRAM



RECOMMENDED P.C.B. LAYOUT  
安装尺寸图

PRODUCT NO. : 1TS005\*\*\*\*\*-\*\*\*\*\* AB - CT

轻触开关

6X6系列

外形:

按钮颜色:

底座颜色:

盖板颜色:

操作力度:

160=160gf

260=260gf

手感:

0=常规

1=大手感

2=小手感

3=特殊手感

材料:

0=初始材料

1=新增材料

依次增加

产品高度(H):

430=4.30mm

500=5.00mm

非编带

编带, 不启用

| X. ± 0.3   | X' ± 3     | UNITS  | NAME(NTENDED USE)      | HON YUAN                         |
|------------|------------|--------|------------------------|----------------------------------|
| X ± 0.2    | X' ± 2     | MAT'L  | 6X6 T/H SERIES         | HON YUAN PRECISION IND. CO.,LTD. |
| XX ± 0.1   | XX' ± 1    | FINISH | TACT SWITCH            | SHENZHEN, CHINA,                 |
| XXX ± 0.05 | XXX' ± 0.5 |        | PART NO.(NTENDED USE)  | PRODUCT DRAWING                  |
|            |            |        | 1TS005D-2500-4301AB    | 1TS005D-2500-4301AB              |
|            |            |        | APPD: W.P.Lu 2017.1.12 | DWG NO:                          |
|            |            |        | CHKD: S.L.Ji 2017.1.12 | SCALE SHEET REV.                 |
|            |            |        | DR: Y.Y.Chen 2017.1.12 | 10/1 1/1 A                       |