




REVISION	DESCRIPTION	CHECK	APP	DATE	REV.NOTICE.NO
1					
2					
3					


A
B
C
D
E
F
G
H




PCB PATTERN (TOP VIEW)



Insertion




SEC.A-A
Contact Retracted




CONTAC TIP DETAIL

APPL ICABLE IC



PERFORMANCE

- Insulation Resistance: 1000mΩ Min.At DC 500V
- Dielectric Withstanding Voltage For 1 Minute At AC 700V
- Contact Resistance 30mΩ MAX.at 10mA and 20mV MAX.(Initial)
- Operation Temperature -65°C ~+175°C
- Contact Force 18g Per Pin (Normal)
- Life Span 15,000 Times (Mechanical)
- Operation Force 0.9 Kg MAX



6	30-B-4505B	SPRING	SUS	2	FOR COVER
5	210-048-B105D	COVER	PEI	1	BLACK
4	210-048-A105D	BASE	PEI	1	BLACK
3	1013-03LA	CONTACT	BeCu	18	AU PLATING
2	1013-02LA	CONTACT	BeCu	20	AU PLATING
1	1013-01LA	CONTACT	BeCu	18	AU PLATING
No	Part Number	Name	Material	Q'ty	Note

PROJECTION	GENERAL TOLERANCES	FINISH	TITLE
mm	R E V	D	CLASS
SCALE: 1:1	DATE:	DRN NO	
DATE:	DATE:		
DATE:	DATE:		

TSOP66-0.5-01 SOCKET
TSOP-66-0.5-01

