







公差/General tolerances(mm)												0.1/1.0
0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400
~	3	6	10	18	30	50	80	120	180	250	315	400
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20
												±2.50
												±7




剖面图



操作杆

ITEM	NAME OF PART	MATERIAL	NOTES
4	导电件	铜	
3	弹片	不锈钢	301
2	簧片	PC	UL94V-2
1	外壳	PC	UL94V-2

UL 标准/UL Standard:		B	C	D
额定电压/电压/Rated Voltage(V)/Current(A)		300/32	/	450/47
EC 标准/IEC Standard:				
过压类别/Overvoltage Category/污染等级		III/2		
额定电压/电压/Rated Voltage(V)/Current(A)		450/41		
额定脉冲电压(KV)/Rate Impulse Voltage(KV)		4.0		
额定拉力(N·m/Lb·in)		10		
线径范围(硬线和软线)/Wire Range(rigid and flexible)(mm ²)		0.5-6/0.5-4		
间距/Pitch(mm)/线数范围/Poles		6.5/02-05P		
剥线长度/Stripping length(mm)		10-12		
使用温度范围/Operating temperature(°C)		-40~+105		
符合RoHS环保要求/Conform to RoHS		Yes		
标准颜色编号/Standard color number:		通用/灰色		
PANTONE /RAL				

					MATERIAL: /		SURFACE: /	
MAT NO.: /					中国·康伟电子有限公司 KANGWEI Electronics Co., Ltd			
STATUS: /					NAME: KV221-614			
APPD: Lon CHH2020.03.24					DRAWING NO.: KV221-614			
CHKD: Gong YZ2020.03.24					TYPE: CUSTOMER_DRAWING			
DRAFT: CENGWZ_2022.09.30					SCALE:		REV	T001
REV	ECN	DESCRIPTION	DRAFT	DATE	SIZE: A4		SHEET 1/1	
								



中国·康伟电子有限公司
KANGWEI Kangwei Electronics Co., Ltd