






额定负荷	Rating	DC 12V/50mA
接触电阻	Contact Resistance	100mΩ max.
绝缘电阻	Insulation resistance	DC100V 60S 100MΩ min.
抗电强度	Dielectric strength	AC250V(50~60HZ) 60S min.
操作力	Operation force	160±40gf
寿命试验	Operating Life	100,000 cycles
行程	Travels	0.18±0.05mm

规格 Specifications



P . C . B LAYOUT

PRODUCT NO.: 1TS004A*****A1 - CT

轻触开关

3X3系列

外形:

— 产品高度(H):
150=1.50mm

操作力度：一

0=常规(45-75%)

100 100 g
250=250 g

—

— —

45-75%)

484

228

三、感想

— 编带
非编带, 不启用

5	盖板	1	不锈钢	/
6	按钮	1	LCP	灰色
4	防尘膜	1	PI	黄色
3	弹片	2	不锈钢覆银	镀银
2	底座	1	LCP	灰色
1	卡件	1	C5191	镀银
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
X ± 0.3	X* ± 3°	NAME(INTENDED USE)	HON YUAN HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.	
X ± 0.2	X* ± 2°	3X3 SERIES TACT SWITCH		
MAT'L				
.XX ± 0.1	.XX* ± 1°	PART NO.(INTENDED USE)	TITLE:	
.XXX ± 0.05	.XXX* ± 0.5°	1TS004ABB-1600-1500A1	PRODUCT DRAWING	
	FINISH	APPD: W.P.Lu 2017.12.07	DWG NO.: 1TS004ABB-1600-1500A1-CT	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO.,LTD. AND SHALL REMAIN THE PROPERTY OF HON YUAN PRECISION IND. CO.,LTD. IF COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.		Q'TY	CHKD: S.L.li 2017.12.07	
		DR: Y.Y.Chen 2017.12.07		
				
		SCALE 15/1	SHEET 1/1	REV. A