






版次	变更摘要	日期	序号	品名	材质
0			①	A型立式DIP型WTB胶芯 1.25 Pitch S/T Wire To Board Housing DIP (H=4.7)	PA66 UL94V-0 本色(常规用料) Natural/PA66 Conventional material
			②	A型立式DIP型WTB端子 1.25 Pitch S/T Wire To Board Terminal DIP (H=4.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating





技术指标 (Technical Index):

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象. (The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
- 锁扣窗口: 2~3PIN为1个, ≥4PIN为2个.
(Lock Configuration: 2 to 3Pin is 1, ≥4Pin is 2)
- 温度范围 (Temperature range): -25° C~+85° C.
- 额定电压 (Rated voltage): 125V, AC/DC (=等效).
- 接触电阻 (Contact resistance): ≤0.02Ω.
- 绝缘电阻 (Insulation resistance): ≥100MΩ
- 产品料号 (Product material No.):



SECTION A-A

适用线路板 (PCB LAYOUT)



2 PIN 3 PIN
LOCK CONFIGURATION (锁扣位置)



一般公差 (TOLERANCE)
X: ±.50 XX ±1.0
.X ±.20 .XXX ±.05
ANGLES ±1°

Bossie (博锡)			
品名 (TITLE)	单排MX1.25 n*Pin 直针 红色/黄色	制图 (DR)	(CHKD)
料号 (DWG.NO)	BX-MX1.25-nPZZ-R	审核 (APPD)	
比例 (SCALE)	1:1	单位 (UNITS)	mm
张数 (SHEET)	1 OF 1	SIZE	A4
REV	A		