





0,8±0,1

规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60HZ) 60S min.
操作力 Operation force	160±40gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.15±0.05mm



PRODUCT NO.: 1TS004BB\*\*\*\*\*A1 - CT

轻触开关 3X3系列  
 按钮颜色: 底座颜色: 盖板颜色:  
 操作力度: 160=160gf  
 手感: 0=常规 1=大手感 2=小手感 3=特殊手感  
 材质: 0=初始材质 1=新增材质 依次增加  
 产品高度(H): 080=0.8mm  
 非编带 编带

外形:  
 初始颜色 则不启用

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
4	防尘膜	1	PI	黄色
3	弹片	2	SUS301	镀银
2	底座	1	LOP	灰色
1	卡件	1	G5191	镀银

X. ± 0.3	X' ± 3'	UNITS	MM
X ± 0.2	X' ± 2'	MAT'L	
.XX ± 0.1	.XX' ± 1'	FINISH	
.XXX ± 0.05	.XXX' ± 0.5'	Q'TY	

NAME(INTENDED USE)	3X3 SERIES TACT SWITCH	TITLE:	PRODUCT DRAWING
PART NO.(INTENDED USE)	1TS004BB-1600-0800A1-CT	DWG NO.:	1TS004BB-1600-0800A1-CT
APPD:	W.P.Liu 2018.3.31	CHKD:	S.L.Li 2018.3.31
DR:	YY.Chen 2018.3.31	SCALE	15/1
		SHEET	1/1
		REV.	A

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.