





CIRCUIT DIAGRAM



PCB. WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	50 Ω min.
Contact resistance	100mΩ max. initial.
Dielectric Strength	250 V AC(1mn)
Travel	0.2±0.1mm
Storage Temperature	- 30° C to 80° C

E	Button	PPA	1	White
D	COVER	Phosphor copper	1	Silver
C	DOME	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black/White
A	Cards	Phosphor copper	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

Mechanical

P/N	Operating Force(gf)	Height mm	Button	Lead shape (G, J, T)	Ground pin (0, 1)	Pogo Option (0, 1)
YTS2C016	1 160±40	B 5	W (WHITE) B (BLACK)	J	0	0
	2 250±40	A 4.3				

X. ±0.50	X.* ±2°	UNITS mm
.X ±0.30	.X* ±1°	
.XX ±0.10	.XX* ±0.5°	MAT'L
.XXX ±0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD
Email at info@yiyuanswitches.com

FINISH

Q'TY


深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTDPART NO.
YTS2C016TITLE:
TACTILE SWITCH 3.5x6mm

APPD: ROGER

DWG NO.:
YTS2C016

CHKD: RDC

DR: BILLY WANG 2020/08/21

SCALE SHEET REV.
1/1 1/1 A1Packaging:
a reel of 1,500 pieces