

## Specification Sheet

Part Number: MMB10C2



Masonry Mounts provide a permanent solution when fastening wire and cables to masonry surfaces.

The mounts have easy installation into predrilled holes allowing for faster use.

Masonry Cable Tie Mount, 1.712"L, 0.312" Hole Dia, 0.18" Max Cable Tie Width, PA66STHS, Black, 100/pkg

Article Number 151-00326

Type MMB1

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton Masonry Mounts provide a permanent method of attaching wire and cable to masonry surfaces. Masonry mounts simply tap into predrilled holes and can be used for indoor and outdoor applications.

Short Description Masonry Cable Tie Mount, 1.712"L, 0.312" Hole Dia, 0.18" Max Cable Tie Width, PA66STHS, Black, 100/pkg

Global Part Name MMB1-PA66STHS-BK

Length L (Imperial)	1.712
Length L (Metric)	43.5
Fixation Method	Threaded bolt
Width W (Imperial)	0.508
Width W (Metric)	12.9
Cable Ties	T18 - T50
Height H (Imperial)	.50
Height H (Metric)	12.70
Cable Tie Width Max (Imperial)	0.18
Cable Tie Width Max (Metric)	4.6
Mounting Hole Diameter D (Imperial)	0.312
Mounting Hole Diameter D (Metric)	8.0 mm
Mounting Hole Diameter D Max (Metric)	8.0
Material	Polyamide 6.6, super tough, heat stabilized (PA66STHS)
Material Shortcut	PA66STHS

Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)