




技术特性/Specifications:

额定电压 Rated voltage: 250V AC, DC

额定电流 Rated current: 3A AC, DC

接触电阻 Contact resistance: 20m Ω max

绝缘电阻 Insulation resistance: 1000M Ω min

耐压 Withstand voltage: 1000V AC/minute


环境温度 Ambient temperature: -40 $^{\circ}$ C ~ +105 $^{\circ}$ C

适用线规 Wire range: AWG#28 ~ #22

1	2	3	4	5	6	7	8
REV.	REVISION DESCRIPTION					DATE	APPD


NOTES

Available in 02 through 12 Circuits.
Mates with DL25007-R Series Housing.
Material : Nylon UL94V-0(2).
Accepts DL25007-T Crimp Terminal.



Circuits	Product name	Dimension mm	
		A	B
2	SM-2Y	2.50	5.50
3	SM-3Y	5.00	8.00
4	SM-4Y	7.50	10.50
5	SM-5Y	10.00	13.00
6	SM-6Y	12.50	15.50
7	SM-7Y	15.00	18.00
8	SM-8Y	17.50	20.50
9	SM-9Y	20.00	23.00
10	SM-10Y	22.50	25.50
11	SM-11Y	25.00	28.00
12	SM-12Y	27.50	30.50

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE: 2.50 mm Pitch			
.XX: ± 0.15	.X° : ± 2.0°	DL25007 (SM) -Y		Wire To Wire Housing			
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21/12/30	PART NO:			
FINISH:		CHKD: Wu Hui	DATE:21/12/30	SCALE: N/A		PAGE: 1/1	
DRAWING NO:		APPD:Ren An De	DATE:21/12/30	UNITS: mm		REV.: A	



NOTES

Available in 02 through 12 Circuits.
Mates with DL25007-R Series Housing.
Material : Nylon UL94V-0(2).
Accepts DL25007-T Crimp Terminal.




Circuits	Product name	Dimension mm	
		A	B
2	SM-2Y-02	2.50	5.50
3	SM-3Y-02	5.00	8.00
4	SM-4Y-02	7.50	10.50
5	SM-5Y-02	10.00	13.00
6	SM-6Y-02	12.50	15.50
7	SM-7Y-02	15.00	18.00
8	SM-8Y-02	17.50	20.50
9	SM-9Y-02	20.00	23.00
10	SM-10Y-02	22.50	25.50
11	SM-11Y-02	25.00	28.00
12	SM-12Y-02	27.50	30.50

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE: 2.50 mm Pitch			
.XX: ± 0.15	.X° : ± 2.0°	DL25007 (SM)-Y-02		Wire To Wire Housing			
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21/12/30	PART NO:			
FINISH:		CHKD: Wu Hui	DATE:21/12/30	SCALE: N/A		PAGE: 1/1	
DRAWING NO:		APPD:Ren An De	DATE:21/12/30	UNITS: mm		REV.: A	

REV.	REVISION DESCRIPTION	DATE	APPD


NOTES

Available in 02 through 12 Circuits.
Mates with DL25007-Y Series Housing.
Material : Nylon UL94V-0(2).
Accepts DL25007-RT Crimp Terminal.



Circuits	Product name	Dimensino(mm)		
		A	B	C
2	SM-2R	2.5	8.0	5.8
3	SM-3R	5.0	10.5	8.3
4	SM-4R	7.5	13.0	10.8
5	SM-5R	10.0	15.5	13.3
6	SM-6R	12.5	18.0	15.8
7	SM-7R	15.0	20.5	18.3
8	SM-8R	17.5	23.0	20.8
9	SM-9R	20.0	25.5	23.3
10	SM-10R	22.5	28.0	25.8
11	SM-11R	25.0	30.5	28.3
12	SM-12R	27.5	33.0	30.8

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE: 2.50 mm Pitch Wire To Wire Housing	
.XX: ± 0.15	.X° : ± 2.0°	DL25007 (SM) -R		PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21/12/30	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:21/12/30	PAGE: 1/1	
DRAWING NO:		APPD:Ren An De	DATE:21/12/30	UNITS: mm	REV. : A




REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Available in 02 through 12 Circuits.
Mates with DL25007-Y Series Housing.
Material : Nylon UL94V-0(2).
Accepts DL25007-RT Crimp Terminal.

Circuits	Product name	Dimensino (mm)		
		A	B	C
2	SM-2R-02	2.5	8.0	5.8
3	SM-3R-02	5.0	10.5	8.3
4	SM-4R-02	7.5	13.0	10.8
5	SM-5R-02	10.0	15.5	13.3
6	SM-6R-02	12.5	18.0	15.8
7	SM-7R-02	15.0	20.5	18.3
8	SM-8R-02	17.5	23.0	20.8
9	SM-9R-02	20.0	25.5	23.3
10	SM-10R-02	22.5	28.0	25.8
11	SM-11R-02	25.0	30.5	28.3
12	SM-12R-02	27.5	33.0	30.8

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE: 2.50 mm Pitch Wire To Wire Housing	
.XX: ± 0.15	.X° : ± 2.0°	DL25007 (SM) -R-02		PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21/12/30	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:21/12/30	PAGE: 1/1	
DRAWING NO:		APPD:Ren An De	DATE:21/12/30	UNITS: mm	REV. : A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Available in 02 Circuits.

Mates with Y25007XXXX Series Housing.

Material : Nylon UL94V-0(2).

Green Material RoHS Compliant.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
. X: ± 0.25	X° : $\pm 3.0^\circ$	PRODUCT NAME: DL25007 (SM) -2PS		TITLE: 2.50 mm Pitch Wire To Wire Housing	
. XX: ± 0.15	. X° : $\pm 2.0^\circ$	APPD.:Yuan Jun Rong	DATE:21/12/01	PART NO:	
. XXX: ± 0.01	. XX° : $\pm 1.0^\circ$	CHKD.:Wu Hui	DATE:21/12/01	SCALE: N/A	PAGE: 1/1
FINISH: _____		APPD:Ren An De	DATE:21/12/01	UNITS: mm	REV.: A
DRAWING NO:					

1		2		3		4		5		6		7		8	
												REV.	REVISION DESCRIPTION	DATE	APPD

A




B

C

D

E

F




NOTES

Available in 03 through 12 Circuits.
Mates with Y25007XXXX Series Housing.
Material : Nylon UL94V-0(2).
Green Material RoHS Compliant.

Circuits	Product name	Dimension mm	
		A	B
3	SM-3PS	7.5	5.0
4	SM-4PS	10.0	7.5
5	SM-5PS	12.5	10.0
6	SM-6PS	15.0	12.5
7	SM-7PS	17.5	15.0
8	SM-8PS	20.0	17.5
9	SM-9PS	22.5	20.0
10	SM-10PS	25.0	22.5
11	SM-11PS	27.5	25.0
12	SM-12PS	30.0	27.5

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO ., LTD			
. X: ±0.25	X° : ±3.0°	PRODUCT NAME:		TITLE: 2.50 mm Pitch Wire To Wire Housing			
. XX: ±0.15	. X° : ±2.0°	DL25007 (SM) -PS		PART NO:			
. XXX: ±0.01	. XX° : ±1.0°	APPD.:Yuan Jun Rong	DATE:21/12/01	SCALE: N/A			
FINISH:		CHKD.:Wu Hui	DATE:21/12/01	PAGE: 1/1		UNITS: mm	
DRAWING NO:		APPD:Ren An De	DATE:21/12/01	REV.: A			



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Available in 02 through 12 Circuits.


Mates with R25007XXXX Series Housing.

Material : Nylon UL94V-0(2).

Green Material RoHS Compliant.

Circuits	Product name	Dimension mm	
		A	B
2	SM-2RS	5.0	2.5
3	SM-3RS	7.5	5.0
4	SM-4RS	10.0	7.5
5	SM-5RS	12.5	10.0
6	SM-6RS	15.0	12.5
7	SM-7RS	17.5	15.0
8	SM-8RS	20.0	17.5
9	SM-9RS	22.5	20.0
10	SM-10RS	25.0	22.5
11	SM-11RS	27.5	25.0
12	SM-12RS	30.0	27.5

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
. X: ±0.25	X° : ±3.0°	PRODUCT NAME: DL25007(SM)-RS		TITLE: 2.50 mm Pitch Wire To Wire Housing	
. XX: ±0.15	. X° : ±2.0°				
. XXX:±0.01	. XX° :±1.0°	APPD.:Yuan Jun Rong	DATE:21/12/01	PART NO:	
FINISH: _____		CHKD.:Wu Hui	DATE:21/12/01		
DRAWING NO:		APPD:Ren An De	DATE:21/12/01	SCALE: N/A	PAGE: 1/1
				UNITS: mm	REV. : A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in DL25007-Y Series Housing.

Accepts AWG #28~22 Wire Range.






0.06~ 0.33 mm² .

Insulation O.D.=1.2~1.8 mm.


Material : Phosphor Bronze .

Finish: Tin plated.

Thickness: 0.2 mm.



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL25007 (SM)-T	TITLE: 2.5 mm pitch Wire To Wire Crimp Terminal
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:21/05/02
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:21/05/02
FINISH: _____		APPD:Ren An De	DATE:21/05/02
DRAWING NO:		UNITS: mm	PAGE: 1/1 REV.: B



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in DL25007-R Series Housing.
Accepts AWG #28~22 Wire Range.
0.06~ 0.33 mm² .
Insulation O.D.=1.2~1.8 mm.
Material : Phosphor Bronze .
Finish: Tin plated.
Thickness: 0.25 mm.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL25007 (SM) -RT	TITLE: 2.5 mm pitch Wire To Wire Crimp Terminal
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:21/05/02
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:21/05/02	PART NO:
FINISH:		CHKD: Wu Hui	DATE:21/05/02
DRAWING NO:		APPD:Ren An De	DATE:21/05/02
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: B