





公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50



材料及电镀

- ①. 螺 丝: M2.5, 钢, 镀锌, 一字槽
- ②. 塑件主体: PA66, UL94V-0
- ③. 焊 脚: 黄铜, 镀镍
- ④. 方 盒: 黄铜, 镀镍

电气性能

额定电压: 250V
额定电流: 16A
接触电阻: 20mΩ (Max)
绝缘电阻: 500MΩ \DC500V
耐 电 压: AC2000V\1Min
使用线径: 22-14AWG 1.5mm²

机械性能

温度范围: -40℃ ~ +105℃
瞬时温度: +250℃ 5秒
扭 力: 0.4Nm (3.54Lbin)
剥线长度: 4-5mm

Ordering Information

XD301	*	-	*	-	NP	-	*	-	*
Type			PITCH		No. of		Colour		默认=Sorted
V=直针			5.00-5mm		Pins		V=Green		(一字槽)
R=弯针					2/4 Pins		L=Blue		
					2Pin/2Pin		O=Orange		PL=Pinless
					3Pin/3Pin		R=Red		(十字槽)
							B=Black		
							GR=Gray		

			GENERAL TOLERANCE	制 图 DRAWING		 深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL		产品名称 TITLE	5.00 单排 螺丝式 接线端子 直针(一字螺丝)	版本 REV.	A
			X.XX ±0.20	比 例 SCALE		产品料号 PART NO.	XD301V-5.00-NP-V	单 位 UNITS	mm
			X.XXX ±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°						