




Specifications

Coupling : Threaded coupling

Shell material: Zinc alloy with Nickel Plate

Insert material: bakelite

Contact material: copper Silver Plate/Nickel

Termination: Solder


Mating cycle: 500

Cable diameter: -20°C +85°C

Ordering Information

XD - GX12 - NP - *

No. of Pin
2~7 Pin
Contact
Type
F=Female
M=Male



NO. of contacts	芯数	2	3	4	5	6	7
Rated current (A)	额定电流	5A	5A	5A	5A	5A	5A
Operation limit voltage(AC.V.rms)	工作电压(AC.V)分钟	200V	125V	125V	125V	125V	125V
Withstanding voltage(AC.V.rms) 1 minute	耐电压	1500	1500	1500	1500	1500	1500
Insulation resistance (mΩ)	绝缘阻抗	2000	2000	2000	2000	2000	2000
Contact resistance (mΩ)	接触阻抗	5	5	5	5	5	5
Solder cup mouth aperture	焊杯口孔径φ(mm)	φ0.8	φ0.8	φ0.8	φ0.8	φ0.8	φ0.8
Solder inter diameter	接触体孔径φ(mm)	φ1.2	φ1.2	φ1.2	φ1.2	φ1.2	φ1.2

			GENERAL TOLERANCE	制图 DRAWING	 深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd				
			DIM TOL	审核 CHECK					
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	GX12 航空插头 母头	版本 REV.	A	
1	初版发行		X.XX ±0.20	比例 SCALE	产品料号 PART NO.	XD-GX12-NP-F	单位 UNITS	mm	
			X.XXX ±0.10						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投影 Projection		材料 MATERIAL		页次 SHEET	1/1