






公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50



材料及电镀

- ①. 螺 丝: M2.5, 钢, 镀锌, 一字槽
- ②. 塑件主体: PA66, UL94V-0
- ③. 焊 脚: 黄铜, 镀镍
- ④. 方 盒: 黄铜, 镀镍

电气性能

额定电压: 300V
额定电流: 12A
接触电阻: 20mΩ (Max)
绝缘电阻: 500MΩ \DC500V
耐 电 压: AC1600V\1Min
使用线径: 26-14AWG 2.5mm²

机械性能

温度范围: -40℃ ~ +105℃
瞬时温度: +250℃ 5秒
扭 力: 0.4Nm (3.54Lbin)
剥线长度: 6-7mm

Ordering Information

XD127	*	-	*	-	NP	-	*	-	*
Type	Pitch	No. of Pins	Colour						
V=直针 R=弯针	5.00-5mm	2-24 Pin 2Pin-2Pin 3Pin-3Pin	V=Green L=Blue O=Orange R=Red B=Black GR=Gray						

			GENERAL TOLERANCE	制 图 DRAWING		 深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL		产品名称 TITLE	5.00 单排 螺丝式 接线端子 直针(一字螺丝)	版本 REV.	A
1	初版发行		X.XX ±0.20	比 例 SCALE		产品料号 PART NO.	XD127V-5.00-NP-V	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX ±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°						